

Technical data sheet

Fine protection for 9-pole RS232 interface

Item number: 5080053



Data cable protection device for serial interfaces

- Various connection technologies available
- Low voltage protection level

Application: PLC, alarm systems, controllers



Master data		
Item number	5080053	
Type	SD09-V24 9	
Description 1	Data line protection device	
Description 2	for V24 interface D-SUB 9	
Manufacturer	OBO	
Dimension	12V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	6 kg	
Weight unit	kg/100 pc.	

Dimensions		
	Length	60 mm
	Width	16 mm
	Height	34 mm

Technical data sheet

Fine protection for 9-pole RS232 interface

Item number: 5080053



Technical data

Arrestor monitoring	no
Response time	<10 ns
Number of poles	9
Version for	SUB-D-9; V24 RS232
Explosion-tested version	no
Telecommunications contact	no
Maximum continuous voltage AC	12 V
Maximum continuous voltage DC	18 V
Kategorie	Type 3 / C1
Lightning protection zone LPZ	2→3
Mounting type	Connector/cable adapter
Nominal voltage	12 V
Testing standard	IEC 61643-21
Shielding connection available	yes
Screening	Direct
Protection rating	IP40
Protection level wire-wire	<50 V
Protection level, wire-wire at 1 kV/ μs (C3)	<25 V
Protection level wire-earth	<50 V
Protection level, wire-earth at 1 kV/μs (C3)	<25
SPD to IEC 61643-21	Class III / C1
Plug-in system	D-Sub 9-pin
Impulse durability wire-wire	0,34 kA (8/20μs)
Impulse durability wire-earth	0,34 kA (8/20μs)
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C