

Technical data sheet

Fine protection for 15-pole RS232 interface

Item number: 5080150



Data cable protection device for serial interfaces

- Various connection technologies available
- Low voltage protection level

Application: PLC, alarm systems, controllers



Master data		
Item number	5080150	
Type	SD15-V24 15	
Description 1	Data line protection device	
Description 2	for V24 interface D-SUB 15	
Manufacturer	OBO	
Dimension	12V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	7 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,0042 kg CO2e / 1 Piece	

Dimensions		
	Length	60 mm
	Width	16 mm
	Height	41.5 mm

Technical data sheet

Fine protection for 15-pole RS232 interface

Item number: 5080150



Technical data

Arrestor monitoring	no
Response time	<10 ns
Number of poles	15
Version for	SUB-D-15; V24 RS232
Explosion-tested version	no
Telecommunications contact	no
Maximum continuous voltage AC	12 V
Maximum continuous voltage DC	18 V
Kategorie	Type 3 / C1
Lightning protection zone LPZ	2→3
Mounting type	Connector/cable adapter
Nominal voltage	12 V
Testing standard	IEC 61643-21
Shielding connection available	yes
Screening	Direct
Protection rating	IP40
Protection level wire-wire	<50 V
Protection level, wire-wire at 1 kV/ µs (C3)	<25 V
Protection level wire-earth	<50 V
Protection level, wire-earth at 1 kV/µs (C3)	<25
SPD to IEC 61643-21	Class III / C1
Plug-in system	D-Sub 15-pin
Impulse durability wire-wire	0,34 kA (8/20µs)
Impulse durability wire-earth	0,34 kA (8/20µs)
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C