Technical data sheet

Distribution box, 12 division units, with terminal strip, polycarbonate Item number: 2008852





Distribution box with terminal strip for surface mounting, for the current sub-distribution in interior and exterior areas, in accordance with IEC 439-3. With premounted 35 mm hat profile rail. IP66 protection type and IK08 protection rating. Transparent cover to screw on, with cut-out.

- Protection-insulated for a maximum of 12 division units

- Terminal strip set consisting of: One each of: PE/N terminal (1x25 mm² and 1x16 mm² screw terminals, 2x4 mm² and 12x2.5 mm² screwless terminals), mini hat profile rail, mounting instructions and fastening set

- Identification plates for connected consumers
- 8 elastic cable entries Ø20 mm for cable diameters of 0-17 mm
- 1 elastic cable entry Ø25 mm for cable diameters of 0-22 mm
- 1 elastic cable entry Ø32 mm for cable diameters of 0-28 mm
- 10 Ø 20 mm break-out openings each at the top and bottom
- 1 Ø 20/25/32 mm combination break-out opening each at the top and bottom
- 4 screw cover caps
- 2 stainless steel external fastenings
- Cover strips for unused division units Nominal current 63 A



Master data

Item number	2008852
Туре	SDB 12 PC
Description 1	Small distributor
Description 2	for max. 12 distribution units
Manufacturer	OBO
Dimension	286x202x125
Colour	Light grey; RAL 7035
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	150 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to- Gate	6,4826 kg COe / 1 Piece

Technical data sheet

Distribution box, 12 division units, with terminal strip, polycarbonate



Item number: 2008852



Technical data

Extension option	yes
Number of rows	1
Cover type	Cover
Version, small distributor cover	With cut-out
DIN rail	yes
Installation location	Protected outdoor area
EMC version	no
Glow wire test	850 °C
Terminals	Connector
With mounting plate	no
With lock	no
Mounting type, consumer units	Structure
Nominal insulating voltage AC	1000 V
Nominal insulating voltage DC	1500 V
Nominal voltage	400 V
Nominal current	63 A
Protection rating	IP66
Protection rating IK code	IK08
Transparent lid	yes
	-