

# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056644



SKS 60 = Heavy-duty cable tray system with 60 mm side height.  
The cable tray, type SKS, should also be used for the maintenance of electrical function. For additional data, please refer to BSS fire protection systems.  
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



<b>St</b>	Steel
<b>FT</b>	Hot-dip galvanised

### Master data

Item number	6056644
Description 1	Cable tray SKS
Description 2	perforated
Manufacturer	OBO
Dimension	60x150x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	328.7 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	7,7001 kg COe / 1 Meter


# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056644



### Dimensions



Dimension	60 x 150
Length	3,000 mm
Length	10 ft
Width	150 mm
Width	6 in
Height	60 mm
Height	2 in
Plate thickness	0.06 in
Plate thickness	1.5 mm
Dimension B	150 mm
Maß W	150 mm

### Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	yes
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	88 cm²
Usable cross-section	8800 mm²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056644



### Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	3 m
Support spacing 1.5 m	2.65 kN/m
Support spacing 2.0 m	1.8 kN/m
Support spacing 2.5 m	1.15 kN/m
Support spacing 3.0 m	0.5 kN/m

