

# Technical data sheet

## Adjustable bend element 110 FT

Item number: 6225546



Adjustable bend element, heavy-duty, with welded rung for use in the cable ladder types with a side height of 110 mm.



**St** Steel

**FT** Hot-dip galvanised

### Master data

|                     |                         |
|---------------------|-------------------------|
| Item number         | 6225546                 |
| Type                | SLGBE 1190 FT           |
| Description 1       | Adjustable bend element |
| Description 2       | for cable ladder        |
| Manufacturer        | OBO                     |
| Dimension           | 110x900                 |
| Colour              | zinc                    |
| Material            | Steel                   |
| Surface             | Hot-dip galvanised      |
| Surface standard    | DIN EN ISO 1461         |
| Smallest sales unit | 1                       |
| Unit of quantity    | Piece                   |
| Weight              | 305.4 kg                |
| Weight unit         | kg/100 pc.              |


# Technical data sheet

## Adjustable bend element 110 FT

Item number: 6225546



### Dimensions



|             |        |
|-------------|--------|
| Width       | 900 mm |
| Height      | 110 mm |
| Dimension B | 900 mm |
| Dimension R | 900 mm |

### Technical data

|                               |                          |
|-------------------------------|--------------------------|
| Bend (angle)                  | Adjustable               |
| Version of the rungs          | Profile perforated       |
| Side rail version             | Flat profile             |
| Connector version             | Integrated connector     |
| Maintain electrical functions | no                       |
| Change of direction           | Vertical, rising/falling |
| Rustproof steel, pickled      | no                       |
| Hinged                        | yes                      |
| Side perforation              | no                       |
| Wide-span version             | no                       |
| Rail thickness                | 2 mm                     |