

# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056636



SKS 60 = Heavy-duty cable tray system with 60 mm side height.  
The cable tray, type SKS, should also be used for the maintenance of electrical function. For additional data, please refer to BSS fire protection systems.  
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



- St Steel
- FT Hot-dip galvanised

Master data		
Item number	6056636	
Description 1	Cable tray SKS	
Description 2	perforated	
Manufacturer	OBO	
Dimension	60x100x3000	
Colour	zinc	
Material	Steel	
Surface	Hot-dip galvanised	
Surface standard	DIN EN ISO 1461	
Smallest sales unit	3	
Unit of quantity	Metre	
Weight	277 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	6,4055 kg COe / 1 Meter	


# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056636



### Dimensions



Dimension	60 x 100
Length	3,000 mm
Length	10 ft
Width	100 mm
Width	4 in
Height	60 mm
Height	2 in
Plate thickness	0.06 in
Plate thickness	1.5 mm
Dimension B	100 mm
Maß W	100 mm

### Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Walkable	no
Maintain electrical functions	yes
With cover	no
Mounting perforation in base	yes
NATO hole pattern	no
Usable cross-section	58 cm²
Usable cross-section	5800 mm²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	no
Load test type according to IEC 61537	Type II
Type of connector, cable support system	Screwed

# Technical data sheet

## Cable tray SKS 60 FT

Item number: 6056636



### Loads

Insertable support spacings, min.	1.5 m
Insertable support spacings, max.	3 m
Support spacing 1.5 m	2.65 kN/m
Support spacing 2.0 m	1.8 kN/m
Support spacing 2.5 m	1.15 kN/m
Support spacing 3.0 m	0.5 kN/m



### Load diagram, cable tray, type SKS 60

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width