

Technical data sheet

Hot-dip galvanised steel pipe, with thread

Item number: 2046540



Electrical installation pipe according to EN 61386-1 with threaded ends to EN 60423 for mechanical protection of cables.

With burr-free inner wall. Corrosion protection class 4 (high). One coupling is already screwed onto each pipe.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	2046540
Type	SM63W FT
Description 1	Threaded conduit
Description 2	with threaded coupler
Manufacturer	OBO
Dimension	M63, 3000mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	9
Unit of quantity	Metre
Weight	324.7 kg
Weight unit	kg/100 m
CO Footprint (GWP) Cradle-to-Gate	6,7676 kg COe / 1 Meter


Technical data sheet

Hot-dip galvanised steel pipe, with thread

Item number: 2046540



Dimensions



Length	3,000 mm
Dimension D	63 mm
Dimension L	3,000 mm
Dimension I	26 mm
Dimension m (mm)	M63
Dimension t	1.8 mm

Technical data sheet

Hot-dip galvanised steel pipe, with thread

Item number: 2046540



Technical data

Surface-mounted	yes
Pipe version	Rigid with thread
Concrete installation	yes
Bending behaviour	rigid
Pressure resistance	Very heavy (4,000 N)
Use temperature, max.	+ 400 °C
Use temperature, min.	- 45 °C
Thread	M63x1,5
Cavity wall installation	yes
Installation on wood	yes
Installation in the earth	yes
Installation outdoors	yes
Classification code	55571
Machines and system installation	yes
With sleeve	yes
Brushed surface	no
Polished surface	no
Impact resistance	Very heavy (6.8/300 mm)
Permitted temperature range, max.	400 °C
Permitted temperature range, min.	-45 °C
Underfloor installation (bitumen, hot asphalt)	yes
Underfloor installation (screed)	yes
Concealed	yes