


Technical data sheet

Cable ladder SLCS 110, 3 m C30 FT SOMY

Item number: 7186402



Cable ladder with 110 mm side height with welded C30 profile rungs which are open in an upwards direction. Rolled side rail for reinforcement and as edge protection. Fastening to the bracket takes place using clamps, type LKS 40. The slot dimension of the frame is 16.5 mm and the appropriate U clamp clip is type 2056. Magnetic shield insulation without cover 10 dB, with cover 15 dB.



St

Steel

FT
SO

Hot-dip galvanised 85 µm

Master data

Item number	7186402
Type	SLCS 1130 3 FTSO
Description 1	Cable ladder
Description 2	unperforated rung, welded
Manufacturer	OBO
Dimension	110x300x3000
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised 85 µm
Surface standard	DIN EN ISO 1461
Smallest sales unit	30
Unit of quantity	Metre
Weight	571.4 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	12,3903 kg COe / 1 Meter

Item number: 7186402