


# Technical data sheet

90° bend with Z rung, FT

Item number: 7099004



90° bend for shipbuilding cable ladders, type SLZ, with side height of 40 mm with welded, perforated Z rungs.  
Connectors should be ordered separately and in the appropriate quantity.



|    |                    |
|----|--------------------|
| St | Steel              |
| FT | Hot-dip galvanised |

## Master data

|                     |                    |
|---------------------|--------------------|
| Item number         | 7099004            |
| Type                | SLZB 90 300 FT     |
| Description 1       | 90° bend           |
| Description 2       | with Z-rung        |
| Manufacturer        | OBO                |
| Dimension           | B310mm             |
| Colour              | zinc               |
| Material            | Steel              |
| Surface             | Hot-dip galvanised |
| Surface standard    | DIN EN ISO 1461    |
| Smallest sales unit | 1                  |
| Unit of quantity    | Piece              |
| Weight              | 382 kg             |
| Weight unit         | kg/100 pc.         |


# Technical data sheet

90° bend with Z rung, FT

Item number: 7099004



## Dimensions



|        |        |
|--------|--------|
| Width  | 300 mm |
| Height | 40 mm  |

## Technical data

|                               |                    |
|-------------------------------|--------------------|
| Bend (angle)                  | 90°                |
| Version of the rungs          | Profile perforated |
| Side rail version             | Flat profile       |
| Connector version             | Without connectors |
| Maintain electrical functions | no                 |
| Change of direction           | Horizontal         |
| Rustproof steel, pickled      | no                 |
| Hinged                        | no                 |
| Side perforation              | no                 |
| Wide-span version             | no                 |
| Rail thickness                | 5 mm               |