

# Technical data sheet

## US 5 support FT

Item number: 6341578



U support of dimensions 50 x 50 mm with welded head plate.  
For fastening to horizontal concrete ceilings and steel girders. For bracket widths of 400 mm or more, or if the bracket is mounted at the end of a suspended support, we recommend the use of the spacer, type DSK 45.



St

Steel

FT

Hot-dip galvanised

### Master data

Item number	6341578
Description 1	Support
Description 2	with welded head plate
Manufacturer	OBO
Dimension	50x50x600
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	185 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	6,099 kg COe / 1 Piece


# Technical data sheet

## US 5 support FT

Item number: 6341578



### Dimensions



Length	600 mm
Width	50 mm
Height	50 mm
Dimension L	600 mm

### Technical data

Version for	U profile
Bracket length 200	5.75 kN
Bracket length 400	3.1 kN
Bracket length 600	2.2 kN
Maintain electrical functions	yes
Material thickness	2.5 mm
Maximum tensile load	10 kN
With toothing	no


# Technical data sheet

## US 5 support FT

Item number: 6341578



### Loads



#### Load diagram, U support, type US 5 K

- 1 Bending of the end of the suspended support at permitted bracket load
- 2 Permitted bracket load in kN without man load
- 3 Bracket length in mm
- Load curves with support lengths in mm

### Characteristic anchor load values for US 5 K support

Single-sided bracket load		Max. total load F in kN			
		Bracket length in mm			
F kN		100	200	300	400
4.3		3.06	2.31	1.85	1.53
7.6		4.90	4.10	3.24	2.66

Max. total load F = cable weight + cable tray + bracket + suspended support. The tabular values for double-sided loads take the available axis spacing  $a_i = 10$  cm into account. The stated values are based on uncracked concrete of compressive strength C20/25. Please comply with the installation conditions of ETA(anchors).