

Technical data sheet

Junction box T 100 WB, with Wieland socket 6s

Item number: 2007822



Junction box with Wieland sockets, 2s3p, for the connection of cables indoors and in protected outdoor areas. Rectangular design with knock-out entries to the sides and knock-out entries in the bottom. Suitable for wall and ceiling mounting and on mounting panels. With the option of fastening inside and to mount via the corner domes. Cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

Junction box according to DIN EN 60670. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C.
Clear internal dimensions: 136x102x57 mm



PP Polypropylene

| Master data | |
|------------------------------------|---------------------------|
| Item number | 2007822 |
| Type | T 100 WB 6S3 |
| Description 1 | Junction box |
| Description 2 | with Wieland sockets 6s3p |
| Manufacturer | OBO |
| Dimension | 150x116x67 |
| Colour | Light grey; RAL 7035 |
| Material | Polypropylene |
| Smallest sales unit | 1 |
| Unit of quantity | Piece |
| Weight | 29.4 kg |
| Weight unit | kg/100 pc. |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,6256 kg COe / 1 Piece |


Technical data sheet

Junction box T 100 WB, with Wieland socket 6s

Item number: 2007822




Dimensions



| | |
|--------|--------|
| Length | 150 mm |
| Width | 116 mm |
| Height | 67 mm |

Technical data



| | |
|-----------------------------------|--|
| Expandable | yes |
| No. of entries | 4 |
| Type of insertion | Strain relief entries for direct penetrations for cable diameters of 7-21 mm |
| Type of housing penetration | Pre-marking |
| Measured insulation voltage Vi | 500 V |
| Equipment | Miscellaneous |
| Cover | Not transparent |
| Cover fastening | Screwed |
| Entry from rear | yes |
| Entries | 4 |
| Explosion-tested version | no |
| Flame-resistant | acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C |
| Shape | Rectangular |
| Maintain electrical functions | Without |
| For Ex zone | Without |
| For Ex zone gas | Without |
| For Ex zone dust | Without |
| Halogen-free | yes |
| Clear internal dimensions | 136x102x57 mm |
| With screening | no |
| with lid | yes |
| Nominal cross-section, min. | 2.5 mm ² |
| Nominal voltage | 500 V |
| Sealable | yes |
| Protection rating | IP20 |
| Permitted temperature range, max. | 60 °C |
| Permitted temperature range, min. | -5 °C |
| Transparent lid | no |
| Weatherproof | no |