

Technical data sheet

Spreading pliers for sealing insert, splittable cable gland

Item number: 2024900



M25

The ideal aiding tool is the pair of spreading pliers which can be used to open the sealing insert. With this tool, inserting the individual cables is quick and easy.

Place the cable in the spreading pliers, insert the spreading pliers into the sealing separation and then open them. Now the cable can easily be placed into the seal.

The gland set consists of an intermediate support, a cap nut and the seal. Of course, the split locknut is also in the scope of delivery.

Master data		
Item number	2024900	
Type	V-TEC TBZ	
Description 1	Spreading pliers	
Description 2	for V-TEC TB	
Manufacturer	OBO	
Dimension	M25	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	26 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	0,0307 kg COe / 1 Piece	


Technical data sheet

Spreading pliers for sealing insert, splittable cable gland

Item number: 2024900



Dimensions



Length	215 mm
--------	--------

Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
explosion-proof	no
Flat cable gland	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Thread type	Metric
Thread increase	1.5 mm
Fibre-glass reinforced	no
Sealing insert, multiple	no
With locknut	yes
Protection rating	IP67
Splittable gland	yes
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-20 °C
Strain relief option	no