

Technical data sheet

Cap nut cable gland, EMC spring contact, metric thread, nickel-plated

Item number: 2086173



With metric connecting thread to IEC 423, robust EMV cap-nut cable gland with large sealing area. The contact between the gland and braided shield is made using a contact spring. Strain relief, wringing protection and tightness over the whole clamping area. Neoprene sealing ring. Polyamide terminal insert. With pre-mounted O sealing ring on connection thread, protection rating IP 68 at 5 bar for 1 hr.

* Prices according to DEL notation.



Brass



Nickel-plated

Master data

Item number	2086173
Type	V-TEC VM25 EMV-K
Description 1	Cable gland EMV
Description 2	contact spring-shielded cable
Manufacturer	OBO
Dimension	M25
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	5.693 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,1484 kg COe / 1 Piece


Technical data sheet

Cap nut cable gland, EMC spring contact, metric thread, nickel-plated

Item number: 2086173



Dimensions



Length	27 mm
Width	30 mm
Height	36.5 mm
Dimension D1	11 mm
Dimension E	30 mm
Dimension G	M25x1,5 mm
Dimension L	29.5 mm
Dimension L1	7 mm
Dimension L2	3.5 mm
Dimension L3	13.3 mm

Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
Sealing area D, max.	16 mm
Sealing area D, min.	11 mm
Flat cable gland	no
For Ex zone	Without
Thread	M25 x 1,5
Thread length	7 mm
Fibre-glass reinforced	no
Halogen-free	no
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF	27
Protection rating	IP68
Permitted temperature range, max.	100 °C
Permitted temperature range, min.	-20 °C
Strain relief option	yes