

Technical data sheet

Plug-in arrester V10 150 V

Item number: 5093400



Surge arrester, type 2+3 to EN 61643-11

- Plug-in upper part; upper part can be separated from base without tools
- Incl. thermal and dynamic cut-off unit and visual display of defects
- High current conductivity and long service life



Master data		
Item number	5093400	
Description 1	SurgeController V10	
Description 2	plug-in arrester	
Manufacturer	OBO	
Dimension	150V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	2.9 kg	
Weight unit	kg/100 pc.	

Dimensions		

Technical data sheet

Plug-in arrester V10 150 V

Item number: 5093400



Technical data

Arrester surge current (8/20 µs) [total]	10 kA
Response time	<25 ns
Blow-out	no
Version for	1-pole
Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	no
Maximum continuous voltage AC	150 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	1→3
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	20 kA
Installation type	On basic element
Nominal discharge current (8/20 µs)	10 kA
Nominal voltage AC (50/60 Hz)	150 V
Network form	Other
Test class, type 2	yes
Protection rating	IP20
Protection level	≤0,7
Signalling on device	Visual
SPD to EN 61643-11	Type 2+3
SPD to IEC 61643-1	Class II+III