

Technical data sheet

Cable gland, PG thread, Pure white

Item number: 2022579



Cable gland with PG connection thread in cap nut design, suitable for junction boxes, housings, distributor boxes in private and industrial areas. With strain relief and integrated sealing lip, tested according to DIN EN 62444. Protection class IP68. Can be used between -20°C and $+65^{\circ}\text{C}$.
Table column D: sealing range to VDE 0619, in which no strain relief is required.
Table column D2: Sealing range including strain relief and twist protection to VDE 0619



PA Polyamide

Master data

Item number	2022579
Type	V-TEC PG16 RW
Description 1	Cable gland
Manufacturer	OBO
Dimension	PG16
Colour	Pure white; RAL 9010
Material	Polyamide
Smallest sales unit	25
Unit of quantity	Piece
Weight	1.38 kg
Weight unit	kg/100 pc.


Technical data sheet

Cable gland, PG thread, Pure white

Item number: 2022579



Dimensions



Dimension E	30 mm
Dimension L max.	33 mm
Dimension L min.	25 mm
Dimension L1	10 mm
Dimension L2	6 mm
Dimension L3	19 mm
Dimension L4	11 mm

Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
Sealing area D, max.	14 mm
Sealing area D, min.	7 mm
explosion-proof	no
Flat cable gland	no
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
Thread	Pg 16
Thread type	PG
Thread length	10 mm
Thread increase	1.41 mm
Fibre-glass reinforced	no
Halogen-free	yes
Unstable torque	3.67 Nm
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF	27
Protection rating	IP68
Splittable gland	no
Permitted temperature range, max.	65 °C
Permitted temperature range, min.	-20 °C

Technical data sheet

Cable gland, PG thread, Pure white

Item number: 2022579



Technical data

Strain relief and wringing protection D2, max.	14 mm
Strain relief and wringing protection D2, min.	7 mm
Strain relief option	yes