

Technical data sheet

Cap nut cable gland, metric thread, silver grey, nickel-plated

Item number: 2086042



With metric connecting thread to IEC 423, robust cap nut cable gland with large sealing area. Strain relief, wringing protection and tightness over the whole clamping area. Neoprene sealing ring. Polyamide terminal insert. With pre-mounted O sealing ring on connection thread, VDE-tested to DIN EN 50262, protection rating IP68 at 5 bar for 1 hr, max. permitted ambient temperature -20 to +100°C.

* Prices according to DEL notation.



Brass



Nickel-plated

Master data

Item number	2086042
Type	V-TEC VM32 MS
Description 1	Cable gland
Manufacturer	OBO
Dimension	M32
Material	Brass
Surface	Nickel-plated
Surface standard	
Smallest sales unit	20
Unit of quantity	Piece
Weight	8.457 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,2129 kg COe / 1 Piece


Technical data sheet

Cap nut cable gland, metric thread, silver grey, nickel-plated

Item number: 2086042



Dimensions



Dimension E	36 mm
Dimension L max.	30 mm
Dimension L1	8 mm
Dimension L2	4.5 mm
Dimension L3	18.5 mm

Technical data

Type of seal	Sealing ring
Version for	Straight
Bend protection	no
Sealing area D, max.	21 mm
Sealing area D, min.	14 mm
explosion-proof	no
Flat cable gland	no
For Ex zone	Without
Thread	M32 x 1,5
Thread type	Metric
Thread length	8 mm
Fibre-glass reinforced	no
Halogen-free	no
Unstable torque	12 Nm
Impact category	6
Strain relief category	A
Sealing insert, multiple	no
With locknut	no
Impact-resistant	no
WAF	34
Protection rating	IP68
Hexagonal corner dimension	36 mm

Technical data sheet

Cap nut cable gland, metric thread, silver grey, nickel-plated

Item number: 2086042



Technical data

Permitted temperature range, max.	100 °C
Permitted temperature range, min.	-20 °C
Strain relief option	yes