

Technical data sheet

Surge arrester, 2-pole + NPE 280 V

Item number: 5094653





- Surge arrester, type 2
- Complete unit consisting of upper part and base, pre-mounted and ready for connection
 - Suitable for TN and TT network systems
 - Plug-in upper part; upper part can be separated from base without tools
 - Incl. thermal and dynamic cut-off unit
 - With visual display of defects
 - High current conductivity and long service life
 - Labelled connections

Application example: Residential buildings, single-family homes and industrial
* Complete = cover and base



Master data	
Item number	5094653
Type	V20-C 2+NPE-280
Description 1	SurgeController V20
Description 2	2+1 version
Manufacturer	OBO
Dimension	280V
Smallest sales unit	1
Unit of quantity	Piece
Weight	32.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,2092 kg COe / 1 Piece

Dimensions	
	

Technical data sheet

Surge arrester, 2-pole + NPE 280 V

Item number: 5094653



Technical data

Arrester surge current (8/20 µs) [total]	60 kA
Response time	<25 ns
Blow-out	no
Version for	2+NPE
Pole version	2+N/PE
Structural width in division units (division unit, 17.5 mm)	3
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	no
Maximum continuous voltage AC	280 V
Integrated back-up fuse	no
Conductor cross-section, flexible (fine-wire), min.	25 mm ²
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	1→2
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	40 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	20 kA
Nominal discharge current (8/20 µs) [L-N]	20 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
Test class, type 2	yes
Protection rating	IP20
Protection level	≤1,3
Signalling on device	Visual
SPD to EN 61643-11	Type 2
SPD to IEC 61643-1	Class II