

Technical data sheet

Surge arrester V10 3-pole + NPE with remote signalling 280 V

Item number: 5094931




Surge arrester, type 2+3

- Complete unit consisting of upper part and base, pre-mounted and ready for connection
- Suitable for TN-S and TT network systems
- Incl. thermal and dynamic cut-off unit
- With visual display of defects
- Version ...-FS with remote signalling and potential-free NO contact for function monitoring
- High current conductivity and long service life
- Labelled connections

Application example: Residential buildings, single-family homes



Master data	
Item number	5094931
Description 1	SurgeController V10
Description 2	3+1 version with RS
Manufacturer	OBO
Dimension	280V
Smallest sales unit	1
Unit of quantity	Piece
Weight	37.9 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	1,5036 kg COe / 1 Piece

Dimensions	
	

Technical data sheet

Surge arrester V10 3-pole + NPE with remote signalling 280 V

Item number: 5094931



Technical data

Arrester surge current (8/20 µs) [total]	40 kA
Response time	<25 ns
Blow-out	no
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	4
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	no
Maximum continuous voltage AC	280 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	1→3
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	20 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	10 kA
Nominal discharge current (8/20 µs) [L-N]	10 kA
Nominal discharge current (8/20 µs) [N-PE]	30 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
TN network form	yes
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Test class, type 2	yes
Protection rating	IP20
Protection level	≤1,1
Signalling on device	Visual
SPD to EN 61643-11	Type 2+3
SPD to IEC 61643-1	Class II+III