

Technical data sheet

Surge arrester V10 Compact 150 V

Item number: 5093378



- Surge protective device, compact module, type 2+3
- Surge protection in sub-distributors to VDE 0100-443 (IEC 60364-4-44)
 - Arresting capacity up to 60 kA (8/20) in total
 - Integrated 3+1 solution for TN and TT network systems on 45 mm module width
 - High-performance varistor technology
 - Incl. thermal and dynamic cut-off unit and visual function display
- Application: Sub/storey distribution as well as device protection in rotational current systems.

Master data		
Item number	5093378	
Type	V10 COMPACT 150	
Description 1	V10 Compact	
Manufacturer	OBO	
Dimension	150V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	15.8 kg	
Weight unit	kg/100 pc.	

Dimensions		

Technical data sheet

Surge arrester V10 Compact 150 V

Item number: 5093378



Technical data

	Arrester surge current (8/20 µs) [total]	60 kA
	Response time	<25 ns
	Blow-out	no
	Version for	3+NPE
	Pole version	3+N/PE
	Structural width in division units (division unit, 17.5 mm)	Miscellaneous
	Operating temperature, max.	80 °C
	Operating temperature, min.	-40 °C
	Remote signalling	no
	Follow current quenching capacity (eff) [N-PE]	0.1 kA
	Follow current quenching capacity left	10
	Maximum continuous voltage AC	150 V
	Integrated back-up fuse	no
	Conductor cross-section, flexible (fine-wire), min.	10 mm ²
	Conductor cross-section, rigid (single-wire/multiwire), max.	10 mm ²
	Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
	Lightning protection zone LPZ	1→3
	Max. mains-side overcurrent protection	63
	Maximum back-up fuse	63 A
	Maximum discharge current (8/20 µs)	20 kA
	Installation type	DIN rail 35 mm
	Nominal discharge current (8/20 µs)	10 kA
	Nominal voltage AC (50/60 Hz)	120 V
	Network form	Other
	TN network form	yes
	TN-C-S network form	yes
	TN-S network form	yes
	TT network form	yes
	Test class, type 2	yes
	Test class, type 3	yes
	Protection rating	IP20
	Protection level	≤0,7
	Signalling on device	Visual
	SPD to EN 61643-11	Type 2+3
	SPD to IEC 61643-1	Class II+III
	Cable type for surge protection devices	Power cable AV