

Technical data sheet

Surge arrester V20, 1-pole 75 V

Item number: 5095141



- Surge arrester, type 2
- For surge voltage protection equipotential bonding to VDE 0100-443 (IEC 60364-4-44)
 - Discharge capacity to 40 kA (8/20) per pole through high-performance varistors
 - Modular connectable arrester with cut-off unit and visual status display
 - Locking mechanism with vibration protection and voltage keying
 - Plastic to UL 94 V-0
 - The remote signalling variants (FS) have a potential-free changeover contact for remote signalling
- Application: Equipotential bonding in main and sub-distributions.



Master data		
Item number	5095141	
Type	V20-1-75	
Description 1	SurgeController V20	
Description 2	1-pole	
Manufacturer	OBO	
Dimension	75V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	11.5 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,59 kg CO2e / 1 Piece	


Technical data sheet

Surge arrester V20, 1-pole 75 V


Item number: 5095141



Dimensions



Technical data



Arrester surge current (8/20 μ s) [total]	40 kA
Connection cross-section (min.)	1.5 mm ²
Response time	<25 ns
Response time [L-N]	25 ns
Blow-out	no
Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Torque	35 Lbs
Torque	4 Nm
Installation location	Interior
Remote signalling	no
Function/defect display	Visual
Housing material surge protection components	PA UL 94 V-0
Maximum continuous voltage (L-N)	75 V
Maximum continuous voltage AC	75 V
Integrated back-up fuse	no
Short-circuit resistant	yes
Short-circuit resistance for max. mains-side overcurrent protection	25 kA
Conductor cross-section, flexible (fine-wire), max.	35 mm ²
Conductor cross-section, flexible (fine-wire), max.	2 AWG
Conductor cross-section, flexible (fine-wire), min.	16 AWG
Conductor cross-section, flexible (fine-wire), min.	1.5 mm ²
Conductor cross-section, rigid (single-wire/multiwire), max.	2 AWG
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	16 AWG
Conductor cross-section, rigid (single-wire/multiwire), min.	1.5 mm ²
Humidity, max.	95 %


Technical data sheet

Surge arrester V20, 1-pole 75 V

Item number: 5095141



Technical data



Humidity, min.	5 %
Max. mains-side overcurrent protection	160 A gL/gG
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	40 kA
Maximum discharge current (8/20 µs) [L-N]	40 kA
Minimum distance	1.5 mm
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	20 kA
Nominal discharge current (8/20 µs) [L-N]	20 kA
Nominal voltage AC (50/60 Hz)	60 V
Network form	Other
TN network form	yes
TN-C network form	yes
TN-C-S network form	yes
TN-S network form	yes
TT network form	yes
Pole number	1
Ports	One-Port SPD
Test class, type 2	yes
Residual voltage [L-N] @ 1 kA	0.3 kV
Residual voltage [L-N] @ 5 kA	0.4 kV
Protection rating	IP20
Protective conductor current	< 250 µA
Protection level	≤0,5
Protection level [L-N]	≤0,5
Signalling on device	Visual
SPD to EN 61643-11	Type 2
SPD to IEC 61643-1	Class II
SPD to UL 1449	Type 4
Permitted temperature range, max.	80 °C
Permitted temperature range, min.	-40 °C
TOV voltage [L-N] – fail safe mode – 120 min.	115 V
TOV voltage [L-N] – withstand mode – 5 s	90 V
Approvals	VDE KEMA UL ÖVE