

Technical data sheet

Base V20 and V25 3pole +NPE with remote signaling

Item number: 5095859



Base

- Suitable for V 25-B+C or V 20-C and C 25-B+C
- With remote signalling and potential-free changeover contact for function monitoring
- Pre-mounted and ready for connection
- With protection against incorrect insertion
- For TN-S and TT network systems
- Labelled connections



Master data		
Item number	5095859	
Type	V20-C U-3+NPE-FS	
Description 1	Bottom part V20 and V25	
Description 2	with remote signalling + NPE	
Manufacturer	OBO	
Dimension	3+NPE+FS	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	34 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,8307 kg COe / 1 Piece	

Dimensions		

Technical data sheet

Base V20 and V25 3pole +NPE with remote signaling

Item number: 5095859



Technical data

Version for	3-pole with NPE; with RS; base
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	5
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Protection rating	IP20
Signalling on device	None