

Technical data sheet

Base V20 and V25 2pole with remote signaling

Item number: 5096316



Base

- Suitable for V 25-B+C or V 20-C
- With remote signalling and potential-free changeover contact for function monitoring
- Pre-mounted and ready for connection



Master data		
Item number	5096316	
Type	V20-C U-2 FS	
Description 1	Bottom part V20 and V25	
Description 2	with remote signalling	
Manufacturer	OBO	
Dimension	3-polig	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	22 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,5177 kg COe / 1 Piece	


Technical data sheet

Base V20 and V25 2pole with remote signaling

Item number: 5096316



Dimensions



Technical data

Version for	2-pole with RS; lower part
Pole version	2
Structural width in division units (division unit, 17.5 mm)	3
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Protection rating	IP20
Signalling on device	None