

Technical data sheet

Combination arrester V25, 4-pole 280 V with remote signalling

Item number: 5094493



Combination arrester, lightning and surge arrester type 1+2

- Complete unit consisting of upper part and base, pre-mounted and ready for connection
- Suitable for TN networks
- With remote signalling and potential-free NO contact for function monitoring
- Voltage protection level < 0.9 kV
- Plug-in arrester with dynamic cut-off unit
- Visual function display
- Encapsulated, non-extinguishing zinc oxide varistor arrester for use in standard distributor housings
- Labelled connections
- FS variant with remote signalling contact (potential-free NO contact)

Application example: Buildings with open-wire power supply or for setting up lightning protection equipotential bonding in residential buildings.
* Complete = Top and bottom section
With alarm system (potential-free change-over contact FS)



Master data		
Item number	5094493	
Description 1	CombiController V25	
Description 2	4-pole with remote signalling	
Manufacturer	OBO	
Dimension	280V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	53.2 kg	
Weight unit	kg/100 pc.	
CO Footprint (GWP) Cradle-to-Gate	1,4181 kg COe / 1 Piece	

Dimensions		

Technical data sheet

Combination arrester V25, 4-pole 280 V with remote signalling

Item number: 5094493



Technical data

Arrester surge current (8/20 µs) [total]	120 kA
Response time	<25 ns
Blow-out	no
Version for	4-pole with FS
Pole version	4
Structural width in division units (division unit, 17.5 mm)	4
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	7 kA
Lightning surge current (10/350)	25 kA
Remote signalling	yes
Follow current quenching capacity I _{eff}	25
Maximum continuous voltage AC	280 V
Maximum continuous voltage DC	200 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	160
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	50 kA
Nominal discharge current (8/20 µs)	30 kA
Nominal discharge current (8/20 µs) [L-N]	30 kA
Nominal discharge current (8/20 µs) [N-PE]	30 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
TN network form	yes
TN-C network form	yes
TN-C-S network form	yes
TN-S network form	yes
Pole number	4
Protection rating	IP20
Protection level	≤0,9
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II