

Technical data sheet

Base, MultiBase with acoustic signalling

Item number: 5096372




- Suitable for V 25-B+C, V 20-C and V 10-C
- With remote signalling, potential-free changeover contact, for function monitoring
- With acoustic signalling for function monitoring, signal tone can be shut down for 24 h
- Pre-mounted and ready for connection



Master data

Item number	5096372
Type	V20-C U-3+NPE-AS
Description 1	Bottom part V20 and V25
Description 2	NPE + acoustic signalling
Manufacturer	OBO
Dimension	3+NPE+AS
Smallest sales unit	1
Unit of quantity	Piece
Weight	32.5 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,844 kg COe / 1 Piece

Dimensions



Technical data sheet

Base, MultiBase with acoustic signalling

Item number: 5096372



Technical data

Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	5
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Installation type	DIN rail 35 mm
Network form	Other
Protection rating	IP20
Signalling on device	Optical and acoustic