

Technical data sheet

CombiController V25, plug-in arrester 320 V

Item number: 5097290



- Combination arrester – type 1+2
- Plug-in arrester can be separated from base without tools and current cut-off in base
 - Including thermal and dynamic cut-off unit and visual fault display
 - High current conductivity and long service life



Master data		
Item number	5097290	
Type	V25-B+C 0-320	
Description 1	CombiController V25	
Description 2	plug-in arrester	
Manufacturer	OBO	
Dimension	320V	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	8 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	0,1104 kg COe / 1 Piece	

Dimensions		

Technical data sheet

CombiController V25, plug-in arrester 320 V

Item number: 5097290



Technical data

Arrester surge current (8/20 µs) [total]	30 kA
Response time	<25 ns
Blow-out	no
Version for	1-pole
Pole version	1
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	7 kA
Lightning surge current (10/350)	7 kA
Remote signalling	no
Maximum continuous voltage AC	320 V
Maximum continuous voltage DC	420 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	160
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	50 kA
Installation type	On basic element
Nominal discharge current (8/20 µs)	30 kA
Nominal voltage AC (50/60 Hz)	320 V
Network form	Other
Pole number	1
Protection rating	IP20
Protection level	≤1,3
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II