

Technical data sheet

MCR protection for 2-pole for power supply, 60 V

Item number: 5097623



Surge protective device/fine protection type 3 to EN 61643-11

- Suitable for DC and AC voltage systems
- With visual function display
- With installation-friendly, screwless connection terminals
- In a space-saving 17.5 mm grid
- Y circuit

Application: Universal use on 35 mm DIN profile rail in every normal commercial-ly available distributor housing.



Master data		
Item number	5097623	
Description 1	Lightning barrier	
Description 2	for AC and DC	
Manufacturer	OBO	
Dimension	60V AC	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	8 kg	
Weight unit	kg/100 pc.	

Dimensions	


Technical data sheet

MCR protection for 2-pole for power supply, 60 V

Item number: 5097623



Technical data



Response time	<25 ns
Blow-out	no
Version for	60 V version
Pole version	2
Structural width in division units (division unit, 17.5 mm)	1
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Explosion-tested version	no
Remote signalling	no
Maximum continuous voltage AC	80 V
Maximum continuous voltage DC	110 V
Conductor cross-section, flexible (fine-wire), min.	2.5 mm ²
Conductor cross-section, rigid (single-wire/multiwire), max.	2.5 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	0.14 mm ²
Lightning protection zone LPZ	2→3
Max. mains-side overcurrent protection	20
Maximum back-up fuse	20 A
Maximum discharge current (8/20 µs)	2 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	0.7 kA
Nominal voltage AC (50/60 Hz)	60 V
Network form	Other
OBO_Nominal load current (input/output terminal)	20 A
Pole number	3
Test class, type 3	yes
Protection rating	IP20
Protection level	≤0,28
Protection level wire-wire	<280 V
Protection level wire-earth	<1200 V
Signalling on device	Visual
SPD to EN 61643-11	Type 3
SPD to IEC 61643-1	Class III
Cable type for surge protection devices	Power cable AV