

Technical data sheet

Combination arrester V25, 3-pole 280 V

Item number: 5094423



- Combination arrester, lightning and surge arrester type 1+2
- Complete unit consisting of upper part and base, pre-mounted and ready for connection
 - For TN systems
 - Plug-in arrester with dynamic cut-off unit
 - With visual function display
 - Protection level decoded:705:Value:RAM1; kV
 - Encapsulated, non-extinguishing zinc oxide varistor arrester for use in standard distributor housings
 - Labelled connections
- Application example: Buildings with open-wire power supply or for setting up lightning protection equipotential bonding in residential buildings.
- * Complete = Plug-in arrester and base



Master data	
Item number	5094423
Description 1	CombiController V25
Description 2	3-pole version
Manufacturer	OBO
Dimension	280V
Smallest sales unit	1
Unit of quantity	Piece
Weight	42.5 kg
Weight unit	kg/100 pc.
CO Footprint (GWP) Cradle-to-Gate	0,9924 kg COe / 1 Piece

Dimensions	

Technical data sheet

Combination arrester V25, 3-pole 280 V

Item number: 5094423



Technical data

Arrester surge current (8/20 µs) [total]	90 kA
Response time	<25 ns
Blow-out	no
Version for	3-pole
Pole version	3
Structural width in division units (division unit, 17.5 mm)	3
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 µs)	7 kA
Lightning surge current (10/350 µs) [N/PE]	25 kA
Lightning surge current (10/350)	21 kA
Remote signalling	no
Follow current quenching capacity I _{eff}	25
Maximum continuous voltage AC	280 V
Maximum continuous voltage DC	200 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	160
Maximum back-up fuse	160 A
Maximum discharge current (8/20 µs)	50 kA
Nominal discharge current (8/20 µs)	30 kA
Nominal discharge current (8/20 µs) [L-N]	30 kA
Nominal discharge current (8/20 µs) [N-PE]	30 kA
Nominal voltage AC (50/60 Hz)	230 V
Network form	Other
TN network form	yes
TN-C network form	yes
Pole number	3
Test class, type 2	yes
Protection rating	IP20
Protection level	≤0,9
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2
SPD to IEC 61643-1	Class I+II