

# Technical data sheet

## Surge arrester, 3-pole + NPE with remote signalling 150 V

Item number: 5094764



### Surge arrester, type 2

- Complete unit consisting of upper part and base, pre-mounted and ready for connection
- Suitable for TN and TT network systems
- Plug-in cover; cover can be separated from base without tools
- With remote signalling and potential-free NO contact for function monitoring
- Incl. thermal and dynamic cut-off unit
- With visual display of defects
- High current conductivity and long service life
- Labelled connections


Application example: Residential buildings, single-family homes and industrial  
\* Complete = cover and base



### Master data

Item number	5094764
Type	V 20-C 3+NPE+FS
Description 1	SurgeController V20
Description 2	3+1 with remote signalling
Manufacturer	OBO
Dimension	150V
Smallest sales unit	1
Unit of quantity	Piece
Weight	41.3 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,4043 kg COe / 1 Piece

### Dimensions



# Technical data sheet

Surge arrester, 3-pole + NPE with remote signalling 150 V

Item number: 5094764



## Technical data

Arrester surge current (8/20 µs) [total]	80 kA
Response time	<25 ns
Blow-out	no
Version for	3+NPE + FS
Pole version	3+N/PE
Structural width in division units (division unit, 17.5 mm)	4
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Remote signalling	yes
Maximum continuous voltage AC	150 V
Integrated back-up fuse	no
Conductor cross-section, flexible (fine-wire), min.	25 mm <sup>2</sup>
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm <sup>2</sup>
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm <sup>2</sup>
Lightning protection zone LPZ	1→2
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 µs)	40 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 µs)	20 kA
Nominal voltage AC (50/60 Hz)	130 V
Network form	Other
Test class, type 2	yes
Protection rating	IP20
Protection level	≤0,8
Signalling on device	Visual
SPD to EN 61643-11	Type 2
SPD to IEC 61643-1	Class II