

Technical data sheet

PV combination arrester V50, 600 V DC

Item number: 5093623



V50 combination arrester, type 1+2, for photovoltaic systems

- Complete unit, consisting of plug-in varistor arrester with cut-off unit
- Error-resistant Y circuit to VDE 0100-712 (EN 50539-12)
- Surge protection equipotential bonding to VDE 0100-443 (IEC 60364-4-44)
- Arresting capacity up to 12.5 kA (10/350) and 50 kA (8/20) per pole
- Low DC protection level: < 2.6 kV and Voc max = 600 V DC
- With visual function display for use in distributor housings

Application: PV systems with lightning protection system.



Master data

Item number	5093623
Type	V50-B+C 3-PH600
Description 1	CombiController V50
Description 2	three-pole for photovoltaics
Manufacturer	OBO
Dimension	600V DC
Smallest sales unit	1
Unit of quantity	Piece
Weight	41 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,0101 kg CO2e / 1 Piece


Technical data sheet

PV combination arrester V50, 600 V DC


Item number: 5093623



Dimensions



Technical data



Arrester surge current (8/20 μ s) [total]	30 kA
Response time	<25 ns
Blow-out	no
Version for	3-pole for PV systems
Pole version	3
Structural width in division units (division unit, 17.5 mm)	3
Operating temperature, max.	80 °C
Operating temperature, min.	-40 °C
Lightning surge current (10/350 μ s)	12.5 kA
Remote signalling	no
Maximum continuous voltage DC	600 V
Conductor cross-section, rigid (single-wire/multiwire), max.	35 mm ²
Conductor cross-section, rigid (single-wire/multiwire), min.	2.5 mm ²
Lightning protection zone LPZ	0→2
Max. mains-side overcurrent protection	125
Maximum back-up fuse	125 A
Maximum discharge current (8/20 μ s)	50 kA
Installation type	DIN rail 35 mm
Nominal discharge current (8/20 μ s)	30 kA
Nominal discharge current (8/20 μ s) [L-N]	30 kA
Network form	DC
DC network form	yes
IT network form	no
Other network form	no
TN network form	no
TN-C network form	no
TN-C-S network form	no
TN-S network form	no
TT network form	no
Protection rating	IP20
Protection level	≤2,6
Signalling on device	Visual
SPD to EN 61643-11	Type 1+2


Technical data sheet

PV combination arrester V50, 600 V DC

Item number: 5093623



Technical data



SPD to IEC 61643-1

Cable type for surge protection devices

Class I+II

Power cable DC (PV)