


Technical data sheet

Wall and ceiling bracket FT

Item number: 6363724



Wall and ceiling bracket for universal structural fastening.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	6363724
Type	WDB L 150 FT
Description 1	Wall and ceiling bracket
Description 2	lightweight version
Manufacturer	OBO
Dimension	B150mm
Colour	zinc
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	1
Unit of quantity	Piece
Weight	26 kg
Weight unit	kg/100 pc.


Technical data sheet

Wall and ceiling bracket FT

Item number: 6363724



Dimensions



Length	235 mm
Width	160 mm
Height	186 mm
Dimension A	170 mm
Dimension B	160 mm
Dimension H	186 mm
Dimension H1 (mm)	84
Dimension L	235 mm

Technical data

Version for	Suspension bracket (C clamp)
F in kN ceiling	0.22 kN
F in kN wall	0.22 kN
Maintain electrical functions for width min.	no
Suitable for metric threaded rod	150
Suitable for mesh cable tray	8
Suitable for cable ladder	yes
Suitable for cable tray	yes
Suitable for tray/ladder width	yes
Hole diameter	150 mm
Material thickness	7 mm
Tray fastening	1.25 mm
Adjustable	Screw-on
	no

Wall fastening

Anchor type	Max. load [kN]					
	Bracket length [mm]					
	50	100	150	200	300	400
BZ-U 8-30-41/95	0.40	0.25	0.22	0.30	0.20	0.12

Systemtest in Anlehnung an DIN EN 61537 in Kombination mit Kabeltragsystem RKS-Magic®. Max. Belastung F ges = Kabelgewicht + Kabelrinne + Wand-/Deckenbügel. Die Tragfähigkeitsangaben erhöhen sich um ein Vielfaches beim Einsatz im ungerissenen Beton. Die angegebenen Werte basieren auf Beton der Festigkeitsklasse C20/C25.