


# Technical data sheet

## T and intersection cover, for trunking type WDK 60170

Item number: 6162258



T and intersection cover for changing the direction of the WDK trunking. The fitting is preperforated at the side for the connection of different trunking cross-sections.



**PVC** Polyvinylchloride

### Master data

|                                    |                         |
|------------------------------------|-------------------------|
| Item number                        | 6162258                 |
| Type                               | WDK HK60170CW           |
| Description 1                      | T- and crosspiece cover |
| Manufacturer                       | OBO                     |
| Dimension                          | 60x170mm                |
| Colour                             | Cream; RAL 9001         |
| Material                           | Polyvinylchloride       |
| Smallest sales unit                | 2                       |
| Unit of quantity                   | Piece                   |
| Weight                             | 32.6 kg                 |
| Weight unit                        | kg/100 pc.              |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,678 kg CO2e / 1 Piece |


# Technical data sheet

T and intersection cover, for trunking type WDK 60170

Item number: 6162258



## Dimensions



|             |        |
|-------------|--------|
| Length      | 291 mm |
| Width       | 170 mm |
| Height      | 60 mm  |
| Dimension a | 291 mm |
| Dimension b | 66 mm  |
| Dimension H | 170 mm |

## Technical data

|                                   |              |
|-----------------------------------|--------------|
| Version for                       | Hood fitting |
| Fastening type                    | Lockable     |
| Maintain electrical functions     | no           |
| for duct dimension                | 60 x 170     |
| Protection rating                 | IP30         |
| Protection rating IK code         | IK04         |
| Permitted temperature range, max. | 60 °C        |
| Permitted temperature range, min. | -5 °C        |