


# Technical data sheet

## Flat angle cover, trunking type WDK 60110

Item number: 6022332



Flat angle hood for changing the direction of the WDK trunking.



**PVC** Polyvinylchloride

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 6022332                  |
| Type                               | WDK HF60110GR            |
| Description 1                      | Flat angle cover         |
| Manufacturer                       | OBO                      |
| Dimension                          | 60x110mm                 |
| Colour                             | Stone grey; RAL 7030     |
| Material                           | Polyvinylchloride        |
| Smallest sales unit                | 2                        |
| Unit of quantity                   | Piece                    |
| Weight                             | 14.399 kg                |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 0,3541 kg CO2e / 1 Piece |


# Technical data sheet

## Flat angle cover, trunking type WDK 60110

Item number: 6022332



### Dimensions



|             |        |
|-------------|--------|
| Length      | 149 mm |
| Width       | 110 mm |
| Height      | 60 mm  |
| Dimension a | 149 mm |
| Dimension H | 110 mm |

### Technical data

|                                   |              |
|-----------------------------------|--------------|
| Version for                       | Hood fitting |
| Fastening type                    | Lockable     |
| Maintain electrical functions     | no           |
| for duct dimension                | 60 x 110     |
| Halogen-free                      | no           |
| Trunking depth                    | 60 mm        |
| Protection rating                 | IP30         |
| Protective film                   | no           |
| Protection rating IK code         | IK04         |
| Permitted temperature range, max. | 60 °C        |
| Permitted temperature range, min. | -5 °C        |
| Angle range, max.                 | 90 mm        |
| Angle range, min.                 | 90 mm        |