

Technical data sheet

Wide span cable tray WKSG 110 FS

Item number: 6098123



Wide span cable tray system, perforated, with a side height of 110 mm.
Straight connectors of type WRVL 110 should be ordered separately and in the appropriate quantity.
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



- St

Steel
- FS

Strip galvanized

Master data		
Item number	6098123	
Description 1	Wide span cable tray	
Description 2	perforated, floor beaded	
Manufacturer	OBO	
Dimension	110x500x6000	
Colour	zinc	
Material	Steel	
Surface	Strip galvanized	
Surface standard	DIN EN 10346	
Smallest sales unit	6	
Unit of quantity	Metre	
Weight	1023.34 kg	
Weight unit	kg/100 m	
CO Footprint (GWP) Cradle-to-Gate	25,4908 kg COe / 1 Meter	


Technical data sheet

Wide span cable tray WKSG 110 FS

Item number: 6098123



Dimensions



Dimension	500 x 110
Length	6,000 mm
Width	500 mm
Height	110 mm
Plate thickness	2 mm
Dimension B	500 mm
Dimension H	10 mm
Dimension L	6,000 mm

Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Mounting perforation in base	yes
Usable cross-section	511 cm ²
Usable cross-section	51100 mm ²
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	yes
Magnetic shield insulation with cover	50 dB
Magnetic shield insulation without cover	20 dB
Usable length	6000 mm
Type of connector, cable support system	Screwed

Technical data sheet


Wide span cable tray WKSG 110 FS

Item number: 6098123



Loads

Insertable support spacings, min.	3 m
Insertable support spacings, max.	8 m
Support spacing 3.0 m	2.9 kN/m
Support spacing 3.5 m	2.43 kN/m
Support spacing 4.0 m	2 kN/m
Support spacing 4.5 m	1.72 kN/m
Support spacing 5.0 m	1.5 kN/m
Support spacing 6.0 m	1 kN/m
Support spacing 7.0 m	0.7 kN/m
Support spacing 8.0 m	0.4 kN/m



Load diagram, wide span cable tray, type WKSG 110

- 1 Permitted cable tray/ladder load in kN/m without man load
- 2 Support width in m
- 3 Rail bend in mm at permitted kN/m
- 4 Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width