

# Technical data sheet

## Wide span cable tray WKSG 160 A2

Item number: 6098571



Wide span cable tray system, perforated, with a side height of 160 mm.  
Straight connectors of type WRVL 160 should be ordered separately and in the appropriate quantity.  
Magnetic shield insulation without cover 20 dB, with cover 50 dB.



- A2

Stainless steel
- 2B

Bright, treated

Master data

Item number	6098571
Type	WKSG 162 A2
Description 1	Wide span cable tray
Description 2	perforated, floor beaded
Manufacturer	OBO
Dimension	160x200x6000
Colour	stainless steel
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	6
Unit of quantity	Metre
Weight	895.067 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	43,3156 kg CO2e / 1 Meter


# Technical data sheet

## Wide span cable tray WKSG 160 A2

Item number: 6098571



### Dimensions



Dimension	160 X 200
Length	6,000 mm
Width	200 mm
Height	160 mm
Plate thickness	2 mm
Dimension B	200 mm
Dimension L	6,000 mm

### Technical data

Connector version	Without connectors
Mounting system fastening type	Floor Ceiling Wall
Maintain electrical functions	no
Mounting perforation in base	yes
Usable cross-section	302 cm <sup>2</sup>
Usable cross-section	30200 mm <sup>2</sup>
Rustproof steel, pickled	no
Side perforation	yes
Wide-span version	yes
Magnetic shield insulation with cover	50 dB
Magnetic shield insulation without cover	20 dB
Usable length	6000 mm
Type of connector, cable support system	Screwed

# Technical data sheet


## Wide span cable tray WKSG 160 A2

Item number: 6098571



### Loads

Insertable support spacings, min.	3 m
Insertable support spacings, max.	8 m
Support spacing 3.0 m	2.9 kN/m
Support spacing 3.5 m	2.59 kN/m
Support spacing 4.0 m	2.3 kN/m
Support spacing 4.5 m	2.04 kN/m
Support spacing 5.0 m	1.8 kN/m
Support spacing 6.0 m	1.4 kN/m
Support spacing 7.0 m	1 kN/m
Support spacing 8.0 m	0.7 kN/m



### Load diagram, wide span cable tray, type WKSG 160

- 1** Permitted cable tray/ladder load in kN/m without man load
- 2** Support width in m
- 3** Rail bend in mm at permitted kN/m
- 4** Load scheme during testing
- Load curve with cable tray/ladder width in mm
- Strut bend curve according to support width