

Technical data sheet

CML3518 profile rail, slot 17 mm, A2, perforated

Item number: 1104498



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



A2	Stainless steel
2B	Bright, treated

Master data

Item number	1104498
Type	CML3518P1000A2
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	1000x35x18
Material	Stainless steel 1.4301
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Metre
Weight	71 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	3,7966 kg CO2e / 1 Meter


Technical data sheet

CML3518 profile rail, slot 17 mm, A2, perforated

Item number: 1104498



Dimensions



Length	1,000 mm
Width	35 mm
Height	18 mm
Dimension L	1,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Bundle	10 m
Maintain electrical functions	no
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	yes
Slot width	17 mm
Static value A	0.88 cm ²
Static value I _y	0.41 cm ⁴
Static value I _z	0.41 cm ⁴
Static value W _y	1.81 cm ³
Static value W _z	1.03 cm ³