

Technical data sheet

CML3518 profile rail, slot 17 mm, FT, perforated

Item number: 1104560



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1104560
Type	CML3518P0600FT
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	600x35x18
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	10
Unit of quantity	Piece
Weight	45.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,0396 kg CO2e / 1 Piece


Technical data sheet

CML3518 profile rail, slot 17 mm, FT, perforated

Item number: 1104560



Dimensions



Length	600 mm
Width	35 mm
Height	18 mm
Dimension L	600 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value I _y	0.41 cm ⁴
Static value I _z	1.81 cm ⁴
Static value W _y	0.41 cm ³
Static value W _z	1.03 cm ³