

Technical data sheet

CM3518 profile rail, slot 17 mm, perforated

Item number: 1104599



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.




St	Steel
FT	Hot-dip galvanised

Master data

Item number	1104599
Type	CMS3518P2000FT
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	2000x35x18
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	20
Unit of quantity	Metre
Weight	102.9 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	2,2879 kg CO2e / 1 Meter

Dimensions



Length	2,000 mm
Width	35 mm
Height	18 mm
Dimension L	2,000 mm

Technical data sheet

CM3518 profile rail, slot 17 mm, perforated

Item number: 1104599



Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Maintain electrical functions	yes
Material thickness	1.75 mm
With perforation	yes
With tothing	no
Profile shape	C profile
ROHS-conformant	yes
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value Iy	0.41 cm ⁴
Static value Iz	1.81 cm ⁴
Static value Wy	0.41 cm ³
Static value Wz	1.03 cm ³