

Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104320



Light-duty profile rail, perforated, slot width 17 mm.



- St Steel
- FS Strip galvanised

Master data	
Item number	1104320
Type	CML3518P0800FS
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	800x35x18
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	10
Unit of quantity	Piece
Weight	56.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	1,4251 kg CO2e / 1 Piece


Technical data sheet

CML3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104320



Dimensions



Length	800 mm
Width	35 mm
Height	18 mm
Dimension L	800 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.25 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	0.88 cm ²
Static value I _y	0.41 cm ⁴
Static value I _z	1.81 cm ⁴
Static value W _y	0.41 cm ³
Static value W _z	1.03 cm ³