

Technical data sheet

CMS3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104349



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FS	Strip galvanised

Master data

Item number	1104349
Type	CMS3518P0150FS
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	150x35x18
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	25
Unit of quantity	Piece
Weight	14.67 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,3749 kg CO2e / 1 Piece


Technical data sheet

CMS3518 profile rail, slot 17 mm, FS, perforated

Item number: 1104349



Dimensions



Length	150 mm
Width	35 mm
Height	18 mm
Dimension L	150 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	25 mm
Maintain electrical functions	yes
Material thickness	1.75 mm
With perforation	yes
With tothing	no
Profile shape	C profile
Rustproof steel, pickled	no
Slot width	17 mm
Static value A	1.17 cm ²
Static value I _y	0.52 cm ⁴
Static value I _z	0.53 cm ⁴
Static value W _y	2.33 cm ³
Static value W _z	1.33 cm ³