


Technical data sheet

CL2518 profile rail, slot 17 mm, FS, perforated

Item number: 1111640



Central C profile rail for cable routing, in conjunction with clamp clips with a hammerhead foot. Can also be used as suspension construction for cable support systems.



St	Steel
FS	Strip galvanised

Master data

Item number	1111640
Type	C2518
Description 1	Profile rail
Description 2	perforated, slot 17mm
Manufacturer	OBO
Dimension	2000x25x18
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	55 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,3803 kg CO2e / 1 Meter


Technical data sheet

CL2518 profile rail, slot 17 mm, FS, perforated

Item number: 1111640



Dimensions



Length	2,000 mm
Width	25 mm
Height	18 mm
Dimension L	2,000 mm

Technical data

Type of perforation	Perforated back
Version for	Single profile
Maintain electrical functions	no
Hole shape (ETIM)	Long slot
Material thickness	1.25 mm
With perforation	yes
With tothing	no
Profile shape	C profile
ROHS-conformant	yes
Slot width	17 mm
Static value A	0.67 cm ²
Static value Iy	0.26 cm ⁴
Static value Iz	0.78 cm ⁴
Static value Wy	0.21 cm ³
Static value Wz	0.75 cm ³