

Technical data sheet

Hat profile rail, unperforated GTP

Item number: 1115421



Hat profile rail 35 x 15 mm similar to DIN EN 60715 (formerly DIN EN 50022), but with material thickness 1.5 mm.



St

Steel


GTP

Electrogalvanised, transparently-passivated

Master data

Item number	1115421
Type	2069 15 1.5 GTP
Description 1	Top hat rail
Description 2	unperforated, 1.5 mm thick
Manufacturer	OBO
Dimension	2000x35x15
Material	Steel
Surface	Electrogalvanised, transparently-passivated
Surface standard	
Smallest sales unit	2
Unit of quantity	Metre
Weight	66 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	1,1921 kg CO2e / 1 Meter

Dimensions



Length	2,000 mm
Width	35 mm
Height	15 mm

Technical data sheet

Hat profile rail, unperforated GTP

Item number: 1115421



Technical data

Version for	Unperforated
Version, rails	Support rail DIN EN 60715
Bundle	20 m
Hole shape (ETIM)	Without
Material thickness	1.5 mm