

Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121466



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FT	Hot-dip galvanised

Master data

Item number	1121466
Type	MS5030P3000FT
Description 1	Profile rail
Description 2	perforated, slot 22mm
Manufacturer	OBO
Dimension	3000x50x30
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	3
Unit of quantity	Metre
Weight	308.1 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	6,0294 kg CO2e / 1 Meter


Technical data sheet

MS5030 mounting rail, slot 22 mm, FT, perforated

Item number: 1121466



Dimensions



Length	3,000 mm
Width	50 mm
Height	30 mm
Dimension L	3,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Material thickness	3 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	22 mm
Static value A	3.39 cm ²
Static value I _y	3.99 cm ⁴
Static value I _z	13.11 cm ⁴
Static value W _y	3.95 cm ³
Static value W _z	6.38 cm ³