

Technical data sheet

CL2510 profile rail, 11 mm slot, FS, perforated

Item number: 1108123



Light-duty C profile rail for cable routing, in conjunction with series clips or clamp clips with N foot. Can also be used in building of control cabinets. Perforated, cannot be broken.



St	Steel
FS	Strip galvanised

Master data

Item number	1108123
Type	CL2510P2000FS
Description 1	Profile rail
Description 2	perforated, slot 11mm
Manufacturer	OBO
Dimension	2000x25x10
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	2
Unit of quantity	Metre
Weight	36.8 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	0,9293 kg CO2e / 1 Meter


Technical data sheet

CL2510 profile rail, 11 mm slot, FS, perforated

Item number: 1108123



Dimensions



Length	2,000 mm
Width	25 mm
Height	10 mm
Dimension L	2,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	10 mm
Bundle	50 m
Maintain electrical functions	no
Material thickness	1 mm
With perforation	yes
With toothing	no
Profile shape	C profile
Slot width	11 mm
Static value A	0.44 cm ²
Static value I _y	0.06 cm ⁴
Static value I _z	0.44 cm ⁴
Static value W _y	0.12 cm ³
Static value W _z	0.35 cm ³