

Technical data sheet

MS4141PP mounting rail, slot 22 mm, FT, perforated

Item number: 1122501



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



- St Steel
- FT Hot-dip galvanised

Master data		
Item number	1122501	
Type	MS4141PP0400FT	
Description 1	Profile rail	
Description 2	perforated, slot 22mm	
Manufacturer	OBO	
Dimension	400x41x41	
Material	Steel	
Surface	Hot-dip galvanised	
Surface standard	DIN EN ISO 1461	
Smallest sales unit	1	
Unit of quantity	Piece	
Weight	90 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	2,2664 kg CO2e / 1 Piece	


Technical data sheet

MS4141PP mounting rail, slot 22 mm, FT, perforated

Item number: 1122501



Dimensions



Length	400 mm
Width	41 mm
Height	41 mm
Dimension L	400 mm

Technical data

Breakable	no
Type of perforation	3 sides perforated
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Hole size	11x25
Material thickness	2.5 mm
With perforation	yes
With toothing	yes
Profile shape	C profile
Slot width	22 mm
Static value A	2.42 cm ²
Static value I _y	6 cm ⁴
Static value I _z	6.97 cm ⁴
Static value W _y	2.49 cm ³
Static value W _z	2.88 cm ³