

Technical data sheet

Beam clamp SSP 6-21, VA M8

Item number: 1486284



This type of support clamp is pushed onto the support and fixed to the girder or flat iron using a pressure trough and bolt (M8). The hexagonal bolt has a WAF of 10 mm. In the clip element also two more M8 threads are introduced, for example to attach threaded rods.



A2	Stainless steel
2B	Bright, treated

Master data		
Item number	1486284	
Type	SSP 6-21 M8 A2	
Description 1	Beam clamp	
Description 2	heavyweight design	
Manufacturer	OBO	
Dimension	6-21mm	
Material	Stainless steel 1.4301	
Surface	Bright, treated	
Surface standard		
Smallest sales unit	25	
Unit of quantity	Piece	
Weight	23.2 kg	
Weight unit	kg/100 pc.	
CO2 Footprint (GWP) Cradle-to-Gate	1,1494 kg CO2e / 1 Piece	


Technical data sheet

Beam clamp SSP 6-21, VA M8

Item number: 1486284



Dimensions



Dimension B	48 mm
Dimension H	46 mm
Dimension L	47 mm

Technical data

Connection type/component	Thread
Fastening type	Clamp
Breaking load F1	1.75 kN
Breaking load F2	1.5 kN
Flange thickness F max.	21 mm
Flange thickness F min.	6 mm
Suitable for metric threaded rod	8
Thread	M8
Thread metric	8
ROHS-conformant	yes
Hinge, adjustable	no
Hinged	no