

# Technical data sheet

## Beam clamp SSP 20-40, VA M8

Item number: 1486292



This type of support clamp is pushed onto the support and fixed to the girder or flat iron using a pressure trough and bolt (M8). The hexagonal bolt has a WAF of 10 mm. In the clip element also two more M8 threads are introduced, for example to attach threaded rods.



|    |                 |
|----|-----------------|
| A2 | Stainless steel |
| 2B | Bright, treated |

### Master data

|                                    |                          |
|------------------------------------|--------------------------|
| Item number                        | 1486292                  |
| Type                               | SSP 20-40 M8 A2          |
| Description 1                      | Beam clamp               |
| Description 2                      | heavyweight design       |
| Manufacturer                       | OBO                      |
| Dimension                          | 20-40mm                  |
| Material                           | Stainless steel 1.4301   |
| Surface                            | Bright, treated          |
| Surface standard                   |                          |
| Smallest sales unit                | 25                       |
| Unit of quantity                   | Piece                    |
| Weight                             | 27.8 kg                  |
| Weight unit                        | kg/100 pc.               |
| CO2 Footprint (GWP) Cradle-to-Gate | 1,3105 kg CO2e / 1 Piece |


# Technical data sheet

## Beam clamp SSP 20-40, VA M8

Item number: 1486292



### Dimensions



|             |       |
|-------------|-------|
| Dimension B | 48 mm |
| Dimension H | 65 mm |
| Dimension L | 47 mm |

### Technical data

|                                  |        |
|----------------------------------|--------|
| Connection type/component        | Thread |
| Fastening type                   | Clamp  |
| Breaking load F1                 | 1.4 kN |
| Breaking load F2                 | 1.3 kN |
| Flange thickness F max.          | 40 mm  |
| Flange thickness F min.          | 20 mm  |
| Suitable for metric threaded rod | 8      |
| Thread                           | M8     |
| Thread metric                    | 8      |
| ROHS-conformant                  | yes    |
| Hinge, adjustable                | no     |
| Hinged                           | no     |