

Technical data sheet

Lower part plug-in junction box

Item number: 2006216



Pluggable lower part of junction box. Unequipped, without cover. Halogen-free material and UV-resistant. Flame-resistant to DIN EN 60695/2/11, test temperature 650 °C. Impact resistance IK07 at room temperature. Protection rating IP30.



PP Polypropylene

Master data

Item number	2006216
Type	UT01 SW
Description 1	Plug-in junction box
Description 2	lower part, black
Manufacturer	OBO
Dimension	150x116x62
Colour	Graphite black; RAL 9011
Material	Polypropylene
Smallest sales unit	40
Unit of quantity	Piece
Weight	11 kg
Weight unit	kg/100 pc.


Technical data sheet

Lower part plug-in junction box

Item number: 2006216



Dimensions



Length	150 mm
Width	116 mm
Height	62 mm

Technical data

Expandable	yes
Type of entry	Cable/pipe
Type of housing penetration	Pre-marking
Measured insulation voltage Vi	500 V
Equipment	Without
Cover fastening	Screwed
Entry from rear	yes
Entries	10
Explosion-tested version	no
Flame-resistant	acc. to VDE 0471/DIN 695 Part 2-1, test temperature 650°C
Shape	Rectangular
Maintain electrical functions	Without
For Ex zone	Without
For Ex zone gas	Without
For Ex zone dust	Without
for pipe diameter	16/19 mm
Halogen-free	yes
Max. Conductor cross-section	10 mm ²
With screening	no
with lid	no
Mounting in the earth	no
Mounting underwater	no
Mounting type	Wall/ceiling mounting
Sealable	yes
Protection rating	IP30
Protection rating IK code	IK07.
Permitted temperature range, max.	65 °C
Permitted temperature range, min.	-25 °C
Transparent lid	no
Castable	no
Sealing compound supplied	no
Weatherproof	no