

Technical data sheet

MSL4141 mounting rail, slot 22 mm, FS, perforated

Item number: 1122974



Heavy-duty C profile rail for individual installation of support constructions, e.g. for cable trays or as a panel for switchgear cabinets. Can also be used for cable routing, in conjunction with clamp clips with a U foot.



St	Steel
FS	Strip galvanised

Master data

Item number	1122974
Type	MSL4141P6000FS
Description 1	Profile rail
Description 2	perforated, slot 22mm
Manufacturer	OBO
Dimension	6000x41x41
Material	Steel
Surface	Strip galvanised
Surface standard	DIN EN 10346
Smallest sales unit	6
Unit of quantity	Metre
Weight	201.1 kg
Weight unit	kg/100 m
CO2 Footprint (GWP) Cradle-to-Gate	4,772 kg CO2e / 1 Meter


Technical data sheet

MSL4141 mounting rail, slot 22 mm, FS, perforated

Item number: 1122974



Dimensions



Length	6,000 mm
Width	41 mm
Height	41 mm
Dimension L	6,000 mm

Technical data

Breakable	no
Type of perforation	Perforated back
Version for	Single profile
Drill hole spacing, centre	50 mm
Maintain electrical functions	yes
Hole size	14x28
Material thickness	2 mm
With perforation	yes
With tothing	yes
Profile shape	C profile
ROHS-conformant	yes
Slot width	22 mm
Static value A	2.45 cm ²
Static value Iy	5.18 cm ⁴
Static value Iz	7.56 cm ⁴
Static value Wy	2.51 cm ³
Static value Wz	2.69 cm ³