

Technical data sheet

Beam clamp SSP 20-40, FT M8

Item number: 1486288



This type of support clamp is pushed onto the support and fixed to the girder or flat iron using a pressure trough and bolt (M8). The hexagonal bolt has a WAF of 10 mm. In the clip element also two more M8 threads are introduced, for example to attach threaded rods.



St

Steel

FT

Hot-dip galvanised

Master data

Item number	1486288
Type	SSP 20-40 M8 FT
Description 1	Beam clamp
Description 2	heavyweight design
Manufacturer	OBO
Dimension	20-40mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	25
Unit of quantity	Piece
Weight	27.8 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,5584 kg CO2e / 1 Piece


Technical data sheet

Beam clamp SSP 20-40, FT M8

Item number: 1486288



Dimensions



Dimension B	48 mm
Dimension H	65 mm
Dimension L	47 mm

Technical data

Connection type/component	Thread
Fastening type	Clamp
Breaking load F1	1.4 kN
Breaking load F2	1.3 kN
Flange thickness F max.	40 mm
Flange thickness F min.	20 mm
Suitable for metric threaded rod	8
Thread	M8
Thread metric	8
ROHS-conformant	yes
Hinge, adjustable	no
Hinged	no