

Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Terminals made of brass, screws of steel, galvanised and transparently passivated, 12-pole, strip separable into individual terminals, only open on one side.

Closed on one side, captive upwards screw.


Nominal cross-section $2.5 \div \text{mm}^2$.

Nominal voltage 250 V.

Nominal current 24 A.

Max. connectable cross-sections per terminal: $4 \times 2.5 \text{ mm}^2$, $5 \times 1.5 \text{ mm}^2$ or $6 \times 1 \text{ mm}^2$.

Delivery sorted by colour: 3 black, 2 blue, 3 yellow-green, 1 brown and 1 grey strip in each packaging unit.



PA Polyamide

Master data

Item number	2055201
Type	70 S
Description 1	Dolü branch terminal
Description 2	closed on one side
Manufacturer	OBO
Dimension	$2,5\text{mm}^2$
Colour	(sorted)
Material	Polyamide
Smallest sales unit	10
Unit of quantity	Piece
Weight	2.852 kg
Weight unit	kg/100 pc.
CO2 Footprint (GWP) Cradle-to-Gate	0,2561 kg CO2e / 1 Piece


Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Dimensions



Length	129.6 mm
Width	12 mm
Height	17.5 mm

Technical data sheet

Dolü branch terminals, open on one side

Item number: 2055201



Technical data

Closing plate required	no
Connectable conductor cross-section, single-wire, max.	2.5 mm ²
Connectable conductor cross-section, single-wire, min.	1 mm ²
Connection position	Side
No. of terminals	12
Number of screwless terminals per pole	1
Version of electrical connection 1	Screw connection
Drill hole spacing, centre	11 mm
Explosion-tested version	no
Suitable for flexible conductors	yes
Suitable for solid conductors	no
Suitable for multi-wire conductors	yes
Halogen-free	yes
Insulation material	Thermoplast
Mounting type	Direct mounting
Nominal cross-section, min.	2.5 mm ²
Nominal voltage	250 V
Nominal current	24 A
Pole number	12
Cross-section	Max. connectable cross-sections per terminal: 4 x 2.5 mm ² , 5 x 1.5 mm ² or 6 x 1 mm ² mm ²
ROHS-conformant	yes
Transparent	no